












1) CHEST FREEZERS VT 75... 546

Low temperature freezer	Technical data										
  <u>Castors</u>  <u>Interior</u>  <u>Lock</u>	<table><tr><td>Temperature:</td><td>-10... -45, -30...-60</td></tr><tr><td>Ambient temp. range:</td><td>+16... +25 [°C]</td></tr><tr><td>Power:</td><td>230/50/60 [V/Hz]</td></tr><tr><td>Doors:</td><td>1 pc.</td></tr><tr><td>Nosie level:</td><td>N/A [dB]</td></tr></table> <p>Wersja:</p> <ul style="list-style-type: none">Single compressorDigital displayDigital controller Dixell XR30CXAluminium handleCastorsLockProbe failure alarmVisual & acustic alarmDry contact for remote alarmDoor foamedExterior color whiteExterior material galv. steelInterior color whiteInterior material galv. steel <p>Standard equipment:</p> <ul style="list-style-type: none">ManualWarranty book with a list of service centers  <u>Big control panel</u>	Temperature:	-10... -45, -30...-60	Ambient temp. range:	+16... +25 [°C]	Power:	230/50/60 [V/Hz]	Doors:	1 pc.	Nosie level:	N/A [dB]
Temperature:	-10... -45, -30...-60										
Ambient temp. range:	+16... +25 [°C]										
Power:	230/50/60 [V/Hz]										
Doors:	1 pc.										
Nosie level:	N/A [dB]										

DIFERENT TEMPERATURES -60 ° C AND -45 ° C AND DIFFERENT SIZES

<i>Picture</i>	<i>Temp.</i>	<i>Type</i>	<i>Dimensions[mm]</i>	<i>Capacityé[L]</i>
	-60°C	VT 75	895x600x645	71/74
	-60°C	VT 147	885x720x695	133/140
	-60°C	VT 307	885x1260x695	284/296
	-60°C	VT 407	885x1560x695	368/383
	-60°C	VT 547	890x1660x758	476/495
<i>Picture</i>	<i>Temp.</i>	<i>Type</i>	<i>Dimensions[mm]</i>	<i>Capacity[L]</i>
	-45°C	VT 146	885x720x695	133/140
	-45°C	VT 306	885x1260x695	284/296

	-45°C	VT 406	885x1560x695	368/383
	-45°C	VT 546	890x1660x758	476/495